

PROPERTIES

Safe - the system must only be used with the $\varnothing 1.5$ mm steel cable included in the kit, ensuring the appropriate strength.

Reliable - it is recommended to use a minimum of two suspensions per object to guarantee installation stability.



Practical - height adjustment is simple: press the button and move the cable gripper up or down.

Flexible - allows height adjustment of the system at any time, provided the load is previously removed or supported.

Durable - made of nickel-plated brass and 304 stainless steel, with high wear resistance.

Protected - the cable must be free of oil, paint, rust, or other defects to guarantee safe operation.

Specific use - suitable only for static loads indoors and in dry environments at room temperature.



INSTALLATION

- Fix the ceiling accessory (A) to the ceiling with an M6 screw with a head smaller than $\varnothing 10$ mm.
- Pass the cable (L) through the lower part of A.
- Insert the cable (L) into the plunger (C) and pull it out through the plunger (D) of the cable gripper (B).
- Place the clamp (E) on the panel and fasten it with the screw.

MATERIALS

A: Material: Nickel-plated brass
Size: $\varnothing 16 \times 17$ mm

B: Cable gripper "Loop"
Material: Nickel-plated brass
Size: $\varnothing 9 \times 26$ mm

L: Stainless steel cable 304
Size: $\varnothing 1.5 \times 2000$ mm

E: Iron clamp
Opening: 24 mm

IDEATEC
advanced acoustic solutions

Technical Data Sheet

Review: 1

Page: 1

Sheet N°: 1

Product: IDEAFLOW

Ref: 24mm GRIPPER

Notes: MEASUREMENTS IN MM

Done: Dpto. Técnico

Date: 24/09/2025

Approved:

Date: 24/09/2025

Cancelled:

Date: